## HIOKI

## BATTERY IMPEDANCE METER BT4560

0 ADJ

FUNC

FREQ

COMP

## Laboratory Production line

# A new platform for EIS measurement and equivalent circuit analysis

HIOKI

1.1424 mΩ -0.0575 mΩ

3.85327 v

1.0н₂ 25.6°с

Introducing a measurement solution for R&D and

manufacturing of high-capacity batteries for EVs and ESSs




BT4560 BATTERY IMPEDANCE METER

## BATTERY IMPEDANCE METER BT4560

BT4560 BATTERY IMPEDANCE METER

## A reliable EIS measuring instrument for applications ranging from R&D to manufacturing

The Battery Impedance Meter BT4560 can make EIS measurements quickly and easily in applications ranging from R&D to manufacturing. It delivers high-precision measurement capability for quality control of high-capacity batteries, and it can be expanded into an evaluation system for efficiently measuring multiple batteries. In addition, a new LAN interface simplifies the process of building a testing system, offering additional convenience.



Electrochemical impedance spectroscopy (EIS) is a type of testing that measures a battery's impedance across a broad frequency range using small AC signals. The technique, which yields detailed insights into characteristics such as a battery's internal resistance and electrode reactions, aids in the understanding of battery behavior and performance, making it useful in R&D and quality control applications.

0

## Why choose Hioki for EIS measurement?

#### **Bench-top EIS measurement**



- A compact EIS instrument that doesn't require a electronic load device
- Simultaneous measurement of impedance, voltage, and temperature
- Convenient evaluation application software for R&D use
- Compatibility with third-party equivalent circuit analysis software

BT4560 basic performance			
Impedance	Maximum resolution: 0.1 $\mu\Omega$		
Voltage range	$\pm 5$ V, resolution of 10 $\mu$ V		
Measurement current	Max. 1.5 A rms		
EIS measurement frequency	10 mHz to 1050 Hz		

#### Advanced multi-channel solutions Option



- Reduce measurement error with multiplexer circuitry designed with impedance measurement in mind
- Channel switching time: 11 ms
- Ideal for shortening test-times and building reliable testing systems

SW1001 basic performance				
Number of multiplexer slots	3			
Channels	Up to 18 (4-terminal-pair measurement)			
SW1002 basic performance				
Number of multiplexer slots	12			
Channels	Up to 72 (4-terminal-pair measurement)			

#### **Measurement setup**

#### Flexible capability to accommodate a variety of EIS measurement situations

Hioki supplies not only measurement hardware and software, but also clamp fixtures\* to accommodate various battery shapes so that you can build an environment that lets you start evaluating and analyzing batteries right away.

\*Fixtures are special ordered options. Please contact Hioki for assistance.

#### Single-channel




BT4560 + fixture (1 channel)

#### Multi-channel



BT4560 + SW1001 + fixture (6 channels)

## High-precision, high-stability measurement performance Ideal for use with the high-capacity batteries used in EVs and ESSs



The BT4560 can accurately measure high-capacity batteries with internal impedance of less than 1 m $\Omega$ . It provides reproducible data that boosts the reliability of analysis and evaluation.

#### High-precision DC voltage measurement


#### Accuracy: ±0.0035% rdg. ±5 dgt.

Measure a 4 V Li-ion cell with an accuracy of  $\pm 190~\mu V.$ 



This level of precision places the BT4560 on par with a 6 1/2 digit high-precision voltmeter, realizing simutaneous high-precision measurements of battery voltage and impedance.

#### Improve the stability of high-frequency measurement with 4-terminal-pair measurement



4-terminal-pair measurement is a method for using a return wire to cancel magnetic flux caused by the measurement current. Nearby metal objects can cause eddy currents, with measurement variation increasing as the distance to the wire decreases. The 4-terminal-pair method cancels the effects of such eddy currents. This significantly reduces variability in measured values when wires move during measurement. As a result, compared to ordinary 4-terminal measurement, 4-terminal-pair measurement excels at high frequencies measurement (generally about 200 Hz or higher).

#### 4-terminal-pair measurement probes

#### Choose from 2 types depending on the battery's shape



Probes can be adjusted by sliding the stopper to ensure uniform contact position.

#### Pin-Type Probe L2003

For measuring various types of batteries, for example when the instrument is embedded in production line equipment





#### Customers considering embedding the BT4560 in an automated system

Special-order measurement probe cables can be extended to a length of up to 4 m depending on the operating environment. If you need advice concerning system development, for example about topics like fabricating your own probes or wiring, Hioki's global support network can propose solutions quickly and efficiently.

### Data acquisition software that's convenient in R&D work

#### **Computer application software**

#### Easily acquire EIS measurement data



You can easily acquire EIS measurement data using the computer application software that comes with the instrument as a standard accessory. The software can also make measurements at a fixed interval, for example to evaluate the correlation between temperature variations and internal impedance.

#### Measure multiple batteries



Hioki provides software for controlling the SW1001/SW1002 Switch Mainframe to perform EIS measurement of multiple batteries. This software, a standard accessory to both of the switch mainframes, can perform EIS measurement across up to 72 channels, display Nyquist plots in real time. It supports data logging for EIS and single frequency measurement.




#### Circuit Fitting: a simple analysis web app

Find the application here: https://www.circuitfitting.net




This free web application can perform equivalent circuit analysis and create two- and three-dimensional comparative graphs of Nyquist plots (Cole-Cole plots).

#### Automatically display equivalent circuit analysis results




Analyze battery impedance using predefined models. Automatically display analysis results simply by uploading a measurement file.

#### Creation of bode plots to ascertain phase characteristics



Create Bode plots and Nyquist plots simultaneously. Bode plots allow you to ascertain phase characteristics.

#### Analyze characteristics using 3D graphs



Create Nyquist and Bode plots using the time or date as a third axis. Rotate 3D graphs in any direction to review them and export bitmap images.



#### Interoperability with third-party software

## Data compatibility with ZView<sup>®</sup> equivalent circuit analysis software



Import data acquired with the BT4560's standard application software into ZView®\*, a third-party equivalent circuit analysis software package to conduct detailed analysis.

\*ZView® is a trademark of Scribner Associates Inc

#### LabVIEW driver for BT4560




Hioki provides a LabVIEW driver to be used when developing evaluation systems integrated with instruments such as thermostatic chambers and charge/discharge testers. The LabVIEW driver is bundled with a sample application software with functionality for overlaying 5 graphs and conducting simple equivalent circuit analysis.

### **Quality control and inline testing**

Perform low-frequency impedance testing to accommodate the characteristics of high-capacity batteries.

Low-frequency impedance measurement objectives and advantages

- Perform cell screening using zero-cross points<sup>\*1</sup>
- Accumulate data for degradation diagnostics
- Analyze the causes of cell and module defects
- Improve the reproducibility of testing (using measurement at low frequencies can reduce the effects of eddy currents)
- \*1: The frequency point at which X = 0 Ω in a Nyquist plot. In high-capacity batteries, this point tends to shift towards frequencies that are lower than 1 kHz.



#### Example automatic testing system using a multiplexer

You can use the BT4560 to build an automatic testing system that can efficiently measure multiple batteries. You can flexibly expand the number of channels to match your desired test-system size by using the 6-channel Multiplexer Module SW9002 (designed for impedance measurement) and the Switch Mainframe SW1001 or SW1002 (which houses multiplexer modules).



#### Scanning measurement times (reference values)

Number of channels	Measurement frequency	Measurement speed mode	Total time (all channels)	Conditions
6	1 kHz	FAST	0.75 s, approx. 123 ms/ch	
6	1 kHz	MEDIUM	0.95 s, approx. 158 ms/ch	SW1001 + SW9002
6	100 Hz	FAST	0.84 s, approx. 140 ms/ch	RX measurement function
6	100 Hz	MEDIUM	1.25 s, approx. 208 ms/ch	Sample delay: 0 ms (0 waves)
6	1 Hz	FAST	7.50 s, approx. 1250 ms/ch	LAN communication
6	1 Hz	MEDIUM	13.54 s, approx. 2257 ms/ch	

#### **Functionality and interfaces**

#### Functionality suited to automatic testing

The BT4560 provides LAN, RS-232C, and USB communication interfaces along with a range of judgment/data output features needed for automatic testing.

#### Contact check function

By monitoring probes' contact resistance before and after measurement, the instrument can verify that probes have made proper contact with the circuit under measurement.



#### NPN/PNP switching

The BT4560's EXT. I/O circuit can be switched between current sink output (NPN) and current source output (PNP).



(Depth: 293 mm)


#### **Comparator function**

- •Simultaneous judgment of impedance and voltage
- •Overall judgment result output •Two-tone buzzer for checking judgments




#### Panel save/load function

Save up to 126 sets of measurement conditions and load them from the EXT. I/O interface.







#### Accuracy specifications


#### Impedance measurement accuracy (a is as shown in the table below.)

- 3 mΩ range (0.01 Hz to 100 Hz), 10 mΩ range, 100 mΩ range R accuracy =  $\pm$  (0.004 |R| + 0.0017 |X|) [mΩ]  $\pm$  α
- X accuracy =  $\pm$  (0.004 |X| + 0.0017 |R|) [m $\Omega$ ]  $\pm \alpha$
- (The units of R and X are  $[m\Omega]. \, \alpha$  is as shown in the table below.)
- $Z = \pm 0.4\% \text{ rdg.} \pm \alpha (|\sin\theta| + |\cos\theta|)$
- **3** mΩ range (110 Hz to 1050 Hz) R accuracy =  $\pm$  (0.004 |R| + 0.0052 |X|) [mΩ]  $\pm$  α
- X accuracy =  $\pm$  (0.004 |X| + 0.0052 |R|) [m $\Omega$ ]  $\pm \alpha$ (The units of R and X are [m\Omega].  $\alpha$  is as shown in the table below.)
- $Z = \pm 0.4\% \text{ rdg. } \pm \alpha (|\sin\theta| + |\cos\theta|)$  $\theta$  accuracy = ± 0.3°± 57.3  $\frac{\alpha}{7}$  (|sin $\theta$ | + |cos $\theta$ |)
- $\theta$  accuracy = ± 0.1°± 57.3  $\frac{\alpha}{Z}$  (|sin $\theta$ | + |cos $\theta$ |)

		-	2	·	
		Sampling speed	3 mΩ range	10 mΩ range	100 mΩ range
		FAST	25 dgt.	60 dgt.	60 dgt.
α	α	MED	15 dgt.	30 dgt.	30 dgt.
	SLOW	8 dgt.	15 dgt.	15 dgt.	
Temperature coefficient		ture coefficient	R: ± R accuracy × 0.1 / °C; X: ± X accuracy × 0.1 / °C; Z: ± Z accuracy × 0.1 / °C; θ: ± θ accuracy × 0.1 / °C (applied in the ranges of 0°C to 18°C and 28°C to 40°C)		

#### Accuracy graph

3 mΩ range (0.01 Hz to 100 Hz), 10 mΩ range, 100 mΩ range



Impedance accuracy excluding  $\alpha$  (0.004 |R| + 0.0017 |X|, 0.004 |X| + 0.0017 |R|)

#### Voltage measurement accuracy (when self-calibration is performed)

Valtaga	Display range	-5.10000 V to 5.10000 V	
Voltage Resolution		10 µV	
Voltage accuracy	FAST/MED/SLOW	±0.0035% rdg. ±5 dgt.	
Temperature coefficient ±0.0005% rdg. ± 1 dgt. / °C (applied in the ranges of 0°C to 18°C and 28°C to 40°C)			

#### Temperature measurement accuracy (BT4560 + Z2005 temperature sensor)

Accuracy	±0.5°C (measurement temperature: 10.0°C to 40.0°C) ±1.0°C (measurement temperature: -10.0°C to 9.9°C, 40.1°C to 60.0°C)
Temperature coefficient	Temperature coefficient: ±0.01°C / °C (applied in the ranges of 0°C to 18°C and 28°C to 40°C)


#### General Specifications (accuracy guaranteed for 1 year)

Measured items	Impedance, voltage, temperature				
Impedance measu	rement				
Measurement parameters	R resistance, X reactance, Z impedance, θ phase angle				
Measurement frequency	0.01 Hz to 1050 H	z			
Frequency setting resolution	1.0 Hz to 9.9 H 10 Hz to 99 H				
Measurement ranges	3.0000 mΩ, 10.00	)00 mΩ, 100.000 m	Ω		
Allowable input voltage	Up to 5 V				
Measurement/DC- (DC load: offset current ap		ject during impedance	e measurement)		
	3 mΩ range	10 mΩ range	100 mΩ range		
Measurement current	1.5 A rms ±10%	500 mA rms ±10%	50 mA rms ±10%		
DC load current	1 mA or less	0.35 mA or less	0.035 mA or less		
Number of measur	rement current	waves			
	FAST MED SLOW				
0.01 Hz to 66 Hz	1	2	8		
67 Hz to 250 Hz	2	8	32		
260 Hz to 1050 Hz	8	32	128		
Voltage measurem	nent				
Measurement range	5.00000 V (single range)				
Resolution	10 µV				
Measurement time	FAST:0.1 s, MED:0.4 s, SLOW:1.0 s (When self-calibration is performed, 0.21 s is added to the measurement time.)				
Temperature meas	surement				
Display range	-10.0°C to 60.0°C				
Resolution	0.1°C				
Measurement time	2.3 s				

Measurement functions	(R, X, V, T), (Z, θ, V, T), (R, X, T), (Z, θ, T), (V, T)
Functions	Comparator, self-calibration, sample delay, average, voltage limit, potential gradient compensation for im- pedance measurement, charge/discharge prevention during AC signal application, key lock, system test, panel saving and loading (up to 126 condition sets)
Measurement error detection functions	Contact check, measurement current error, voltage drift on measured object, overvoltage input, voltage limit
Interfaces	LAN (TCP/IP, 10BASE-T/100BASE-TX) RS-232C (transmission speed: 9,600 bps/19,200 bps/38,400 bps) USB (pseudo COM port)
EXT. I/O	TRIG, LOAD, Hi, IN, Lo, and others (NPN/PNP can be switched)
Operating temperature and humidity range	0°C to 40°C (32°F to 104°F), 80% RH or less (no condensation)
Storage temperature and humidity range	-10°C to 50°C (14°F to 122°F), 80% RH or less (no condensation)
Operating environment	Indoor, pollution degree 2, altitude up to 2,000 m
Power supplies	Rated supply voltage: 100 to 240 V AC Rated supply frequency: 50/60 Hz
Rated power	80 VA
Dielectric strength	1.62 kV AC, 1 min., cutoff current 10 mA (between all power supply terminals and protective ground)
Applicable standards	Safety: EN61010 EMC EN61326 Class A
Dimensions and weight	Approx. 330W $\times$ 80H $\times$ 293D mm (12.99W $\times$ 3.15H $\times$ 11.54D in.), approx. 3.8 kg (134.0 oz.)
Included accessories	Power cord × 1, instruction manual × 1, zero-adjust- ment board × 1, USB cable (A-B type) × 1, CD-R (comes with communication instruction manual, PC application software, USB driver) × 1



■ 3 mΩ range (110 Hz to 1050 Hz)



Impedance accuracy excluding  $\alpha$  (0.004 |R] + 0.0052 |X|, 0.004 |X| + 0.0052 |R|)

#### **Multiplexer specifications**

#### Switch Mainframe SW1001/SW1002

Number of slots	3 slots (SW1001), 12 slots (SW1002)		
Supported BT4560 module	Multiplexer Module SW9002 (4-terminal-pair, 2-wire)		
Max. input voltage	60 V DC, 30 V AC rms, 42.4 V peak		
Interfaces	LAB, USB, RS-232C (host), RS-232C (command transfer function)		
EXT. I/O	SCAN input, SCAN_RESET input, CLOSE output (scan control)		

#### Multiplexer Module SW9002

Wiring method	4-terminal-pair (6-wire) or 2-wire	
Number of channels	6 channels (4-terminal-pair, 2-wire)	
Contact method	Mechanical relays	
Channel switching time	11 ms (not including measurement time)	
Maximum allowable voltage	60 V DC, 30 V AC rms, 42.4 V peak	
Maximum allowable current	Source: Between HIGH and LOW 2 A DC, 2 A AC rms Sense: Between HIGH and LOW 1 A DC, 1 A AC rms	
Connectors used	D-sub 37-pin pin header	

#### Effect on accuracy of using the instrument with the SW9002<sup>\*1</sup>

BT4560 (connected via L2004)				
	Eff			
Range	Frequency range 0.1 Hz to 100 Hz	Frequency range 110 Hz to 1050 Hz	Conditions, remarks	
3 mΩ R	±0.05% f.s.	±0.1% f.s.	-	
3 mΩ X	±0.1% f.s.	±1.0% f.s.	-	
10 mΩ R	±0.015% f.s.	±0.03% f.s.	-	
10 mΩ X	±0.03% f.s.	-		
100 mΩ R	±0.01% f.s.	±0.01% f.s. ±0.01% f.s.		
100 mΩ X	±0.015% f.s.	±0.03% f.s.	-	
All V ranges ±5 µV			After operating envi- ronment temperature has stabilized within 1 min. after contacts closed	
*1: Effect before zero adjustment.				

Product



#### Model: BATTERY IMPEDANCE METER

SW9002

Connection Cable L2004 BNC, 0.91 m (2.99 ft.)

SW1002

#### Model no. (order code): BT4560-50

Measurement probes are not included with this product. Please separately select and purchase the measurement probe options appropriate for your application.

**Example special specifications** 

measurable battery	Measurement frequency	Measurable battery voltage	Impedance measurement range	Measurement current
/*1	0.01 Hz to 1050 Hz	20 V	30 mΩ, 300 mΩ, 3 Ω	150 mA rms, 50 mA rms, 5 mA rms
ki for more detailed specifica-	*1: No LAN interface			

SW1001

#### Options

Support for a voltage of 20 V

(Please contact Hioki tions.)

#### Probes and sensors



CLIP TYPE PROBE L2002 Cable length: 1.5 m (4.92 ft.)

#### PC connectivity



#### LAN CABLE 9642

Straight, cross conversion connector included, cable length: 5 m (16.40 ft.)



PIN TYPE PROBE L2003TIFCable length: 1.5 m (4.92 ft.)For



TIP PIN 9772-90 For replacing the tip of Pin Type Probe L2003 (one piece)



TEMPERATURE SENSOR Z2005 Cable length: 1 m (3.28 ft.)



4-TERMINAL PROBE L2000

Ideal for clipping to screw terminal, cable length of 1 m (3.28 ft.), cannot be used with 3 mQ range when connected to BT4560, no combined accuracy defined



DISTRIBUITED BY

RS-232C CABLE 9637 For a PC, 9-pin to 9-pin connectors, cross cable, cable length: 1.8 m (5.91 ft.)

Note: company names and product names appearing in this brochure are trademarks or registered trademarks of various companies.

## HIOKI E. E. CORPORATION

#### HEADQUARTERS

81 Koizumi, Ueda, Nagano 386-1192 Japan https://www.hioki.com/



Scan for all regional contact information

## as

TECNOLOGIE DI MISURA

#### CONTATTI E NUMERI UTILI

ASITA SRL Via Malpighi, 170 48018 Faenza (RA)

Asita è anche Centro di Taratura ACCREDIA LAT nº109

Tel. 0546 620559 E-mail. asita@asita.com https://www.asita.com/

All information correct as of Sep. 9, 2024. Contents are subject to change without notice.